

Aluminum ADSS Suspension Clamp, Fixed, .426"-.475" Dia.

By Hubbell Power Systems
Catalog # [HUBSUSF199](#)



Fixed ADSS suspension clamp for .426"-.475" cable diameters.

Features

- Installation with through bolt or banding
- Versatile design can be used as a stringing block (with inserts removed)
- Tangent suspension for spans up to 600 ft.
- Meets IEEE 1591.2

Application

ADSS Cable Suspension

General

Bolt Installation Torque (Recommended)	180 in-lbs
Material - Bolt	Galvanized Steel
Material - Casting	Aluminum Alloy
Material - Washer	Galvanized steel/Neoprene
Product Category	Communications Connectors
UPC	096359665786

Dimensions

Dimensions	6.100 in x 5.600 in x 3.698 in
Height	3.698 in
Length	6.100 in
Weight	2.361 lb
Width	5.600 in

Logistics

Carton Quantity	10
Pallet Quantity	270

Product Assets

[Catalogs - Communication Connectors - Deadends and Splices](#)
[Installation Manuals - Fixed Aluminum ADSS Suspension Clamp Instructions](#)
[Literature - Fixed AL ADSS Susp. Clamp \(SF05114E\)](#)
[Sales Drawings - HUBSUSFxxx Drawing](#)
[Video - Hubbell Power Systems Aluminum ADSS Suspension Clamp Installation \(VI05125E0818\)](#)

Related Products

[HUBSUSH199 - Aluminum ADSS Suspension Clamp, Hanging, .426"-.475" Dia.](#)
[SVD104 - Spiral Vibration Damper, .327"-.461"O.D.](#)