

## Aluminum ADSS Suspension Clamp, Hanging, .426"-.475" Dia.

By Hubbell Power Systems  
Catalog # [HUBSUSH199](#)



Hanging ADSS suspension clamp for .426"-.475" cable diameters.

### Features

- Installation with J-hook or eye-bolt
- Tangent suspension for spans up to 600 ft.
- Meets IEEE 1591.2

### Application

ADSS Cable Suspension

### General

Bolt Installation Torque (Recommended)	180 in-lbs
Material - Bolt	Galvanized Steel
Material - Casting	Aluminum Alloy
Material - Washer	Galvanized steel/Neoprene
Product Category	Communications Connectors
UPC	096359664833

### Dimensions

Dimensions	6.082 in x 2.486 in x 5.483 in
Height	5.483 in
Length	6.082 in
Weight	1.800 lb
Width	2.486 in

### Logistics

Carton Quantity	10
Pallet Quantity	640

### Product Assets

[Installation Manuals - Hanging Aluminum ADSS Suspension Clamp Instructions](#)  
[Literature - Hanging AL ADSS Susp. Clamp \(SF05112E\)](#)  
[Sales Drawings - HUBSUSHxxx Drawing](#)  
[Video - Hubbell Power Systems Aluminum ADSS Suspension Clamp Installation \(VI05125E0818\)](#)

### Related Products

[SVD104 - Spiral Vibration Damper, .327"-.461"O.D.](#)  
[HUBSUSF199 - Aluminum ADSS Suspension Clamp, Fixed, .426"-.475" Dia.](#)