

Dome Closure 350 All Dielectric

By Hubbell Power Systems
Catalog # [PSCA350S](#)

Dome Closure 350 All Dielectric



Features

- Splice capacity: 96 single fusion / 288 mass fusion
- Backbone cable ports accept up to .625" OD
- Lateral cable ports accept up to .625" OD
- Factory equipped for butt splice application
- Additional cables can be added with cable build out kit

General

Cable Diameter for Backbone Ports - Maximum	0.625"
Cable Diameter for Lateral Ports - Maximum	0.625"
Number Of Ports	4
Number of Trays - Maximum	4
Single Fusion Splice Capacity - Maximum	96
UPC	096359707707

Dimensions

Dimensions	21.608 in x 8.575 in x 5.963 in
Height	5.963 in
Length	21.608 in
Weight	7.000 lb
Width	8.575 in

Logistics

Pallet Quantity	48
Standard Package	1

Product Assets

[Catalogs - Fiber Splice Closures \(LEEDS_CONN_CAT_EN_00105\)](#)

[Literature - SF09155E 350 Splice Closure](#)

[Sales Drawings - PSCA350S CC-27210](#)

[Video - Hubbell Power Systems 350 & 570G Fiber Optic Splice Closures \(VI12003E0719\)](#)

Related Products

[PSCSTPS24 - Plastic Splice Tray 24 Fiber Standard Size](#)