

Dome Closure 570 All Dielectric, Grommets

By Hubbell Power Systems
Catalog # [PSCA570SG](#)



Dome Closure 570 All Dielectric, Grommets

Features

- Splice capacity: 432 single fusion / 1152 mass fusion
- Backbone cable ports accept up to .750" OD
- Lateral cable ports accept up to .625" OD
- 2 Grommet bags and stand offs for butt splice included
- Additional cables can be added with cable build out kit

General

Cable Diameter for Backbone Ports - Maximum	0.750"
Cable Diameter for Lateral Ports - Maximum	0.625"
Number Of Ports	6
Number of Trays - Maximum	8
Single Fusion Splice Capacity - Maximum	432
UPC	096359748625

Dimensions

Dimensions	24.550 in x 10.726 in x 7.160 in
Height	7.160 in
Length	24.550 in
Weight	16.800 lb
Width	10.726 in

Logistics

Pallet Quantity	20
Standard Package	1

Product Assets

[Catalogs - Fiber Splice Closures \(LEEDS_CONN_CAT_EN_00105\)](#)
[Installation Manuals - TD09169E ADSS and Isolated G Series Inst](#)
[Literature - SF09168_570 Grommet Splice Closure](#)
[Sales Drawings - PSCA570SG CC-27212](#)
[Video - Hubbell Power Systems 350 & 570G Fiber Optic Splice Closures \(VI12003E0719\)](#)

Related Products

[PSCSTPS24 - Plastic Splice Tray 24 Fiber Standard Size](#)