

ADSS Wedge Deadend, .394-.472" Dia.

By Hubbell Power Systems
Catalog # [WEGADSS102](#)

.394-.472" Diameter Wedge Style Deadend for ADSS Cable



*Representative Image

Features

- .394-.472" Diameter Easy, quick, and safe deadending of ADSS cable
- Installation takes seconds with no special tools
- Standard pack: 30

Application

Dead ending of ADSS cable

General

Material	Polyethylene
Product Category	Communications Connectors
UPC	096359606758

Dimensions

Dimensions	7.870 in x 3.300 in x 1.650 in
Height	1.650 in
Length	7.870 in
Weight	0.884 lb
Width	3.300 in

Logistics

Carton Quantity	30
Minimum Pack Quantity	30

Product Assets

[Catalogs - Communication Connectors - Deadends and Splices](#)
[Literature - ADSS Wedge Style Deadends \(SF05056E\)](#)
[Sales Drawings - CC-23213](#)
[Video - Hubbell Power Systems ADSS Wedge Deadend \(VI0569E\)](#)

Related Products

[WEGADSS101](#)
[WEGADSS103 - ADSS Wedge Deadend, .472-.551" Dia.](#)