



385

Plastic M20 Breather Drain
Increased Safety, Dust Protection
Certified ATEX / IECEx / c CSA us



International Approvals
CE
Ex
IECEx
INMETRO
CSA US

The Hawke plastic breather drain is a cost effective accessory to prevent condensation and drain moisture from hazardous area enclosures. Certified for increased safety and dust protection and dual certified for ATEX/IECEx and NEC/CEC.

Technical Data

Ingress Protection	IP66
Operating Temperature	-60°C to +80°C
Construction Materials	Manufactured in Polyamide with Nitrile O-Ring
Threadform	M20 x 1.5 pitch Thread Length 15mm
ATEX/IECEx	
ATEX/IECEx Protection Class	Ex II 2GD Ex eb IIC Gb; Ex tb IIIC Db
ATEX Certificate No	Baseefa 11ATEX0153X
IECEx Certificate Number	IECEx BAS11.0075X
Construction & Test Standards	IEC/EN 60079-0, IEC/EN 60079-7 and IEC/EN 60079-31
Additional Certifications	Inmetro: IEx 15.0291X
NEC/CEC	
NEC/CEC Protection Class	Class I, Zone 1, AEx e/Ex eb IIC Gb; Zone 21, AEx/Ex tb IIIC Db Class I Division 2, Groups A, B, C, and D; Class II Division 2 Groups E, F, G; Class III
c CSA us Certificate Number	2700364
Construction & Test Standards	CSA C22.2 NO. 0 - 10, CSA 22.2 60079-0, CSA 22.2 60079-1, CSA 22.2 60079-7 and CSA 22.2 60079-31

Ordering Information

Product	Thread Size	Material	Finish
385	M20	N/A	N/A