



Crimp Connectors, Bimetal

By Hubbell

Catalog # [200LUGB8](#)

Crimp connector, 200A BI-METAL 4/0 STR



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Accessory Type	Crimp Connectors
Connector Type	Bimetal
EU RoHS Indicator	No
PROBELOK ? Connectors	No
Type	Tools / Lugs / Parts
UPC	096359392279

Dimensions

Weight	0.1 lb
--------	--------

Electrical Ratings

Current Rating	200 A
----------------	-------

Conductor Related

Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Cable Accessories](#)

[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)

[Sales Drawings - 200 AMP, 15/25 KV Long, Bimetal Connector](#)

[Video - Grease Best PRactices](#)



A Hubbell brand