



Crimp Connectors, ProbeLok Bimetal

By Hubbell
Catalog # 200LUGP4



Crimp connector, 200A BI-METAL PBLK #1 STR

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Accessory Type	Crimp Connectors
Connector Type	ProbeLok Bimetal
EU RoHS Indicator	No
Type	Tools / Lugs / Parts
UPC	096359392354

Dimensions

Weight	0.1 lb
--------	--------

Electrical Ratings

Current Rating	200 A
----------------	-------

Conductor Related

Solid or Compacted Conductor	1/0
Stranded or Compressed Conductor	#1

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)
- [Sales Drawings - 200 AMP, 15/25 KV Probelok Connector](#)
- [Video - Grease Best PRactices](#)



A Hubbell brand