



Crimp Connectors, ProbeLok Bimetal

By Hubbell

Catalog # [200LUGP5](#)

Crimp connector, 200A BI-METAL PBLK 1/0 STR



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Accessory Type	Crimp Connectors
Connector Type	ProbeLok Bimetal
EU RoHS Indicator	No
Type	Tools / Lugs / Parts
UPC	096359392361

Dimensions

Weight	0.1 lb
--------	--------

Electrical Ratings

Current Rating	200 A
----------------	-------

Conductor Related

Solid or Compacted Conductor	2/0
Stranded or Compressed Conductor	1/0

Logistics

Standard Package	1
------------------	---

Product Assets

[Catalogs - Cable Accessories](#)

[Installation Manuals - Recommended Crimp Tools and Dies for 200A Elbow Bi-Metal Connectors](#)

[Sales Drawings - 200 AMP, 15/25 KV Probelok Connector](#)

[Video - Grease Best Practices](#)



A Hubbell brand