

15 Kv Class Elbow Arrester (2.55 kV MCOV)

By Hubbell Power Systems
Catalog # [215ELA03](#)

Deadfront Elbow Arrester, 15kV 2.55 MCOV

Features

To learn more about identifying the right Elbow Arrester on varying applications, visit our blog [here](#).

General

Catalog Number	215ELA03
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359360537

Dimensions

Height	6.6 in
Maximum Operating Altitude	6000 ft
Weight	3.7 lb

Electrical Ratings

Duty Cycle	3 kV
MCOV	2.55 kV
Maximum Discharge Voltage	9.8 kV @ 1.5 kA 10.3 kV @ 3 kA 11 kV @ 5 kA 12.3 kV @ 10 kA 14.3 kV @ 20 kA



Maximum Switching Surge Protective Level @ 500A kV Class	18.5 kV @ 40 kA 8.5 kV 15 kV
--	--

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	160
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Installation Manuals - Elbow Arrester Installation and Operation Instructions](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 15 kV, 200A Loadbreak Elbow Arrester](#)
- [Specifications - 215ELA03](#)
- [Video - Hubbell Power Systems Elbow Arrester](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)
- [Video - Grease Best PRactices](#)