



3-Position Junction W/ Bracket, 15kV

By Hubbell
Catalog # [215J3B](#)



Load Break Junction, 3-Position, 200 Amp, 15 kV, Bracket

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	Brackets
Number of Positions	3
Type	200Amp Load Break
UPC	096359392552

Dimensions

Weight	10.25 lb
--------	----------

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Logistics

Pallet Quantity	25
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - 15kV & 25/28kV 200 Amp Junctions](#)
- [Sales Drawings - 200A 15kV JUNCTION](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - Grease Best Practices](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand