

3-Position Junction W/ U-Straps,  
15kV

By Hubbell Power Systems  
Catalog # [215J3U](#)



Load Break Junction, 3-Position, 200 Amp, 15 kV, U-Straps

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	215J3U
EU RoHS Indicator	No
Mounting Type	U-Straps
Number of Positions	3
Type	200Amp Load Break
UPC	096359385417

Dimensions

Dimensions	11.09 in x 8.500 in x 3.500 in
Height	3.5 in
Length	11.09 in
Weight	5.14 lb
Width	8.5 in

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
------------------------------	-------

Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Carton Quantity	1
Pallet Quantity	144
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - 15kV & 25/28kV 200 Amp Junctions](#)
- [Sales Drawings - 200A 15kV JUNCTION U-STRAPS](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 215J3U](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)
- [Video - Grease Best PRactices](#)