



4-Position Junction W/ U-Straps, 15kV

By Hubbell
Catalog # 215J4U



JUNCTION, 15KV 200A 4-PT U-STRAPS

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	U-Straps
Number of Positions	4
Type	200Amp Load Break
UPC	096359392613

Dimensions

Dimensions	14.9 in x 8.500 in x 3.500 in
Height	3.5 in
Length	14.9 in
Weight	7.5 lb
Width	8.5 in

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Sales Drawings - 200A 15kV JUNCTION U-STRAPS](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand