

15kV Load Break Elbow, 200 Amp,
Size 3

By Hubbell Power Systems
Catalog # [215LE30](#)

Load Break Elbow, 200 Amp, 15 kV.



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, integral seal, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	215LE30
Integral Seal	No
PROBELOK ? Connectors	No
Type	200Amp Load Break
With Seal Kit	No
With Test Point	No

Dimensions

Cable Insulation Diameter Maximum	0.73 in
Cable Insulation Diameter Minimum	0.495 in
Weight	2.75 lb

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
------------------------------	-------

Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	200 A
kV Class	15 kV

Conductor Related

Cable Insulation Diameter Range	0.495 - 0.730
------------------------------------	---------------

Logistics

Pallet Quantity	240
Standard Package	20

Product Assets

- [Catalogs - Cable Accessories](#)
- [Literature - Loadbreak Elbow Infographic](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 215LE30](#)
- [Test Documents - ANSI/IEEE Design Test Report - 15kV 200A Loadbreak Separable Connectors](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems 15kv & 25kv 200A Redesigned Elbow](#)
- [Video - Hubbell Power Systems 200A Loadbreak Elbow Installation](#)