



15kV Parkingstand Arrester (7.65 kV MCOV)

By Hubbell
Catalog # [215PLA09](#)

Deadfront Parkingstand Arrester, 15kV 7.65 MCOV



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Bracket Type	Parkingstand Bracket
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Material	Polymer
Type	Underground Arresters
UPC	096359577058

Dimensions

Height	6.6 in
Maximum Operating Altitude	6000 ft
Weight	4.6 lb

Electrical Ratings

Duty Cycle	9 kV
MCOV	7.65 kV
Maximum Discharge Voltage	26.8 kV @ 1.5 kA
	28 kV @ 3 kA
	30 kV @ 5 kA
	33 kV @ 10 kA
	39 kV @ 20 kA
	50.5 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	23 kV
kV Class	15 kV

Logistics

Pallet Quantity	108
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Underground Arresters](#)
- [Installation Manuals - Parkingstand Arrester Installation and Operating Instructions](#)
- [ISO Certificates - ISO 9001:2015 - Hubbell Power Systems Inc. Effective 2020-2023, Multi-site \(English\)](#)
- [Literature - Application Guide: Metal-oxide Surge Arresters for use on AC systems](#)
- [Sales Drawings - 215PLAXX](#)
- [Video - Grease Best PRactices](#)
- [Video - Hubbell Power Systems Metal Oxide Varistor](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-215PLA09-SPEC-EN | REV 6/2024