

Load Break Bushing Insert, 25kV

By Hubbell Power Systems
Catalog # [225BI](#)



Load Break Bushing Insert, 200 Amp, 25/28 kV.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	225BI
EU RoHS Indicator	No
Type	200Amp Load Break
UPC	096359391586

Dimensions

Dimensions	8.625 in x 3.750 in x 3.750 in
Height	3.75 in
Length	8.625 in
Weight	1.87 lb
Width	3.75 in

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	200 A

kV Class	25/28 kV
----------	----------

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2025)
--------------------------	---

Logistics

Pallet Quantity	640
Standard Package	20

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Loadbreak Connector Installation Instructions](#)
- [Sales Drawings - Insert 25 kV Bushing](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 225BI](#)
- [Test Documents - Cable Accessories Test Report - 25kV Class 200 Amp Loadbreak Separable Connector System](#)
- [Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Grease Best PRactices](#)