



25/28 kV Load Break Feed-Thru, Horizontal

By Hubbell
Catalog # [228FT](#)



Load Break Feed-Thru, Horizontal, 200 Amp, 25/28 kV.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Position	Horizontal
Type	200Amp Load Break
UPC	096359566441

Dimensions

Dimensions	8.50 in x 7.00 in x 4.00 in
Height	4 in
Length	8.5 in
Weight	5.5 lb
Width	7 in

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

Logistics

Pallet Quantity	80
Standard Package	1

Product Assets

[Catalogs - Cable Accessories](#)
[Installation Manuals - Loadbreak Connector Installation and Operating Instructions](#)
[Installation Manuals - IS-200FTI_Rev_A_Oct_2016](#)
[Sales Drawings - Feed -Thru 25 KV](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
[Video - Grease Best PRactices](#)
[Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-228FT-SPEC-EN | REV 6/2024