



## 2-Position Junction W/ U-Straps, 25/28kV

By Hubbell  
Catalog # [228J2U](#)

JUNCTION, 28KV 200A 2-PT U-STRAPS



### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

### General

EU RoHS Indicator	No
Mounting Type	U-Straps
Number of Positions	2
Type	200Amp Load Break
UPC	096359584520

### Dimensions

Dimensions	7.50 in x 8.50 in x 4.000 in
Height	4 in
Length	7.5 in
Weight	5 lb
Width	8.5 in

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

### Logistics

Standard Package	1
------------------	---

### Product Assets

- [Catalogs - Cable Accessories](#)
- [Catalogs - Above Ground Enclosures](#)
- [Interactive Catalog - CA07074E\\_Above Ground Enclosures](#)
- [Sales Drawings - LB Junctions with U-Straps, 25/28 kV](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
HubbellBrand-228J2U-SPEC-EN | REV 6/2024