



## 3-Position Junction W/ Bracket, 25/28 V

By Hubbell  
Catalog # [228J3B](#)



Load Break Junction, 3-Position, 200 Amp, 25/28 kV, Bracket

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

### General

EU RoHS Indicator	No
Mounting Type	Brackets
Number of Positions	3
Type	200Amp Load Break
UPC	096359578949

### Dimensions

Weight	13.59 lb
--------	----------

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

### Logistics

Pallet Quantity	25
Standard Package	1

### Product Assets

[Catalogs - Cable Accessories](#)  
[Installation Manuals - 15kV & 25/28kV 200 Amp Junctions](#)  
[Sales Drawings - LB Junctions with Brackets, 25/28 kV](#)  
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)  
[Test Documents - Cable Accessories Test Report - 28kV Class](#)  
[200A Loadbreak Separable Connectors](#)  
[Video - Grease Best Practices](#)  
[Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand