



3-Position Junction W/ U-Straps, 25/28kV

By Hubbell
Catalog # [228J3U](#)



JUNCTION, 28KV 200A 3-PT U-STRAPS

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	U-Straps
Number of Positions	3
Type	200Amp Load Break
UPC	096359534099

Dimensions

Dimensions	12.50 in x 8.50 in x 4.000 in
Height	4 in
Length	12.5 in
Weight	8.34 lb
Width	8.5 in

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	200 A
kV Class	25/28 kV

Logistics

Pallet Quantity	108
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Sales Drawings - Junction 3P 25 KV](#)
- [Sales Drawings - LB Junctions with U-Straps, 25/28 kV](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Cable Accessories Test Report - 28kV Class 200A Loadbreak Separable Connectors](#)
- [Video - 200A Loadbreak Elbow Fault Closure](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-228J3U-SPEC-EN | REV 6/2024