

15 kV, 600 Amp ETP Kit

By Hubbell Power Systems
Catalog # [615ETPG23](#)

15 kV 600 Amp Elbow Tap Plug Kit. Cable insulation range 0.760 in - 0.950 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	615ETPG23
Connector Type	Aluminum
Type	600 Amp Dead Break
With Seal Kit	No
With Test Point	No

Dimensions

Weight	8.65 lb
--------	---------

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	600 A
kV Class	15 kV



*Representative Image

Conductor Related

Solid or Compacted Conductor	1/0
Stranded or Compressed Conductor	#1

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 600A T-Body Connectors](#)
- [Installation Manuals - Loadbreak Elbow Tap Plug](#)
- [Installation Manuals - Deadbreak Connector 600A, 15/25kV Class T-Body](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 615ETPG23](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems T-Body Connector Assembly](#)
- [Video - Hubbell Power Systems T-Body Assembly with Reducing Taps](#)