



## 15 kV, 600 Amp ETP Kit

By Hubbell  
Catalog # [615ETPJ27](#)

15 kV 600 Amp Elbow Tap Plug Kit. Cable insulation range 0.980 in - 1.180 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Aluminum
EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359437659
With Seal Kit	No
With Test Point	No

### Dimensions

Weight	8.65 lb
--------	---------

### Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	600 A
kV Class	15 kV

### Conductor Related

Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

### Logistics

Pallet Quantity	64
Standard Package	1

### Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Loadbreak Elbow Tap Plug](#)
- [Installation Manuals - Deadbreak Connector 600A, 15/25kV Class T-Body](#)
- [Installation Manuals - Recommended Crimp Tools and Dies for 600A T-Body Connectors](#)
- [Sales Drawings - 615ETP Series 600A, 15KV ETP KIT](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Video - Grease Best Practices](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
HubbellBrand-615ETPJ27-SPEC-EN | REV 6/2024