

15kV Elbow Tap Plug W/ Stud

By Hubbell Power Systems
Catalog # [615ETPS](#)



15 kV 600/200 Amp Elbow Tap Plug with Stud.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	615ETPS
EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359392897

Dimensions

Dimensions	9.500 in x 6.00 in x 5.00 in
Height	5 in
Length	9.5 in
Weight	2.2 lb
Width	6 in

Electrical Ratings

AC Withstand Voltage (1 min)	34 kV
------------------------------	-------

Basic Impulse Level	95 kV
Corona Extinction (3pC)	11 kV
Current Rating	600 A
kV Class	15 kV

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Carton Quantity	3
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Loadbreak Elbow Tap Plug](#)
- [Sales Drawings - Elbow Tap Plug, 15kV \(615ETP\)](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Specifications - 615ETPS](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Grease Best PRactices](#)