



25/28 kV, 600 Amp, T-Body Kit w/ Test Point and Jacket Seal Kit

By Hubbell
Catalog # [625BTJ27TJ](#)

25/28 kV 600 Amp T-Body Kit with Test Point. Cable insulation range 0.980 in - 1.180 in. Kit includes T-body, insulating plug with cap, 4/0 compression lug, threaded stud, cable adapter, and seal kit



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Aluminum
EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359391852
With Seal Kit	Yes
With Test Point	Yes

Dimensions

Weight	8.65 lb
--------	---------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

Conductor Related

Solid or Compacted Conductor	250
Stranded or Compressed Conductor	4/0

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Deadbreak Connector 600A, 15/25kV Class T-Body](#)
- [Sales Drawings - 25/28 kV Deadbreak Elbow Kit](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)
- [Video - Grease Best PRactices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-625BTJ27TJ-SPEC-EN | REV 6/2024