



## 25/28 kV, 600 Amp, T-Body Kit, w/ Jacket Seal kit

By Hubbell  
Catalog # [625BTLM33J](#)

25/28 kV 600 Amp T-Body Kit. Cable insulation range 1.280 in - 1.430 in. Kit includes T-body, insulating plug with cap, 500 compression lug, threaded stud, cable adapter, and seal kit



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Aluminum
EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359438045
With Seal Kit	Yes
With Test Point	No

### Dimensions

Weight	8.65 lb
--------	---------

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

### Conductor Related

Solid or Compacted Conductor	600
Stranded or Compressed Conductor	500

### Logistics

Pallet Quantity	64
Standard Package	1

### Product Assets

[Catalogs - Cable Accessories](#)

[Installation Manuals - Deadbreak Connector 600A, 15/25kV Class T-Body](#)

[Sales Drawings - 25/28 kV Deadbreak Elbow Kit](#)

[SDS - VERSILUBE G661 SILICONE COMPOUND](#)

[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)

[Video - Grease Best PRactices](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
HubbellBrand-625BTLM33J-SPEC-EN | REV 6/2024