



25/28 kV, 600 Amp, T-Body Kit w/ Test Point and shield adapter kit

By Hubbell
Catalog # [625BTN41TS](#)

25/28 kV 600 Amp T-Body Kit with Test Point. Cable insulation range 1.515 in - 1.780 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, cable adapter, and shield adapter kit



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Aluminum
EU RoHS Indicator	No
Type	600Amp Dead Break
UPC	096359589976
With Seal Kit	Yes
With Test Point	Yes

Dimensions

Weight	8.65 lb
--------	---------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	600 A
kV Class	25/28 kV

Conductor Related

Stranded or Compressed Conductor	1000
----------------------------------	------

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

[Catalogs - Cable Accessories](#)

[Sales Drawings - 25/28 kV Deadbreak Elbow Kit](#)

[Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)

[Video - Grease Best PRactices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-625BTN41TS-SPEC-EN | REV 6/2024