

25/28 kV, 600 Amp, T-Body Kit w/
shield adapter kit,

By Hubbell Power Systems
Catalog # [625BTP40S](#)

25/28 kV 600 Amp T-Body Kit. Cable insulation range 1.725 in - 1.935 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, cable adapter, and shield adapter kit

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	625BTP40S
Connector Type	Aluminum
Type	600Amp Dead Break
With Seal Kit	Yes
With Test Point	No

Dimensions

Weight	8.65 lb
--------	---------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV



*Representative Image

Corona Extinction (3pC)	19 kV
Current Rating	600 A
kV Class	25/28 kV

Conductor Related

Solid or Compacted Conductor	1000
Stranded or Compressed Conductor	900

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Cable Accessories](#)
- [Sales Drawings - 25/28 kV Deadbreak Elbow Kit](#)
- [Specifications - 625BTP40S](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems T-Body Connector Assembly](#)
- [Video - Hubbell Power Systems In Depth: T-Body Kits](#)