



# Cable Adapter with Cable Insulation Diameter Range = 0.640 - 0.820 inches

By Hubbell  
Catalog # [625CAF](#)

15/25/28 kV 600/900 Amp Cable Adapter, Cable Insulation  
Diameter Range = 0.640 - 0.820 inches

## Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Tapered design

## General

EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359393054

## Dimensions

Cable Insulation Diameter Maximum	0.82 in
Cable Insulation Diameter Minimum	0.64 in
Weight	1 lb

## Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
Voltage Rating	15 kV

## Conductor Related

Cable Insulation Diameter Range	0.640 - 0.820
------------------------------------	---------------



## Logistics

Carton Quantity	50
Pallet Quantity	1536
Standard Package	1

## Product Assets

- [Catalogs - Cable Accessories](#)
- [Sales Drawings - 625CA](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Video - Grease Best PRactices](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
HubbellBrand-625CAF-SPEC-EN | REV 6/2024