

Cable Adapter with Cable Insulation
Diameter Range = 1.090 - 1.310
inches



By Hubbell Power Systems
Catalog # [625CAK](#)

15/25/28 kV 600/900 Amp Cable Adapter, Cable Insulation
Diameter Range = 1.090 - 1.310 inches

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Tapered design

General

Catalog Number	625CAK
EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359393092

Dimensions

Cable Insulation Diameter Maximum	1.31 in
Cable Insulation Diameter Minimum	1.09 in
Weight	1 lb

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
------------------------------	-------

Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
Voltage Rating	15 kV

Conductor Related

Cable Insulation Diameter Range	1.090 - 1.310
------------------------------------	---------------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	1536
Standard Package	1

Product Assets

[Catalogs - Cable Accessories](#)
[Sales Drawings - 625CA](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Specifications - 625CAK](#)
[Video - Grease Best PRactices](#)