



25/28kV Elbow Tap Plug

By Hubbell
Catalog # [625ETP](#)



25/28 kV 600/200 Amp Elbow Tap Plug.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359383796

Dimensions

Dimensions	9.00 in x 6.00 in x 4.000 in
Height	4 in
Length	9 in
Weight	2 lb
Width	6 in

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

Logistics

Pallet Quantity	144
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - Loadbreak Elbow Tap Plug](#)
- [Sales Drawings - Elbow Tap Plug 25 kV](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Video - Grease Best Practices](#)



A Hubbell brand