

25/28 kV Elbow Tap Plug Kit with
Test Point and Shield Adapter Kit

By Hubbell Power Systems
Catalog # [625ETPK28TS](#)

25/28 kV 600 Amp Elbow Tap Plug Kit with Test Point. Cable insulation range 1.090 in - 1.310 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, cable adapter, and shield adapter kit

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	625ETPK28TS
Connector Type	Aluminum
Type	600Amp Dead Break
With Seal Kit	Yes
With Test Point	Yes

Dimensions

Weight	9.15 lb
--------	---------

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
------------------------------	-------



*Representative Image

Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	200 A
kV Class	25/28 kV

Conductor Related

Solid or Compacted Conductor	300
Stranded or Compressed Conductor	250

Logistics

Standard Package	1
------------------	---

Product Assets

- [Catalogs - Cable Accessories](#)
- [Specifications - 625ETPK28TS](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)
- [Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories](#)
- [Video - Hubbell Power Systems T-Body Connector Assembly](#)
- [Video - Hubbell Power Systems In Depth: T-Body Kits](#)