



## 25/28 kV, 600 Amp ETP Kit

By Hubbell  
Catalog # [625ETPN38](#)

25/28 kV 600 Amp Elbow Tap Plug Kit. Cable insulation range 1.515 in - 1.780 in. Kit includes T-body, insulating plug with cap, 750 compression lug, threaded stud, and cable adapter



\*Representative Image

### Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

### General

Connector Type	Aluminum
EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359392132
With Seal Kit	No
With Test Point	No

### Dimensions

Dimensions	16.688 in x 9.250 in x 5.125 in
Height	5.125 in
Length	16.688 in
Weight	8.65 lb
Width	9.25 in

### Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

### Conductor Related

Solid or Compacted Conductor	900
Stranded or Compressed Conductor	700/750

### Logistics

Pallet Quantity	64
Standard Package	1

### Product Assets

- [Catalogs - Cable Accessories](#)
- [Sales Drawings - 625ETP Series 600A, 25KV ETP KIT](#)
- [Video - Grease Best Practices](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
HubbellBrand-625ETPN38-SPEC-EN | REV 6/2024