



25/28 kV, 600 Amp ETP Kit w/ Test Point

By Hubbell
Catalog # [625ETPN38T](#)

25/28 kV 600 Amp Elbow Tap Plug Kit with Test Point. Cable insulation range 1.515 in - 1.780 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Connector Type	Aluminum
EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359438229
With Seal Kit	No
With Test Point	Yes

Dimensions

Weight	8.65 lb
--------	---------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

Conductor Related

Solid or Compacted Conductor	900
Stranded or Compressed Conductor	700/750

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Sales Drawings - 625ETP Series 600A, 25KV ETP KIT](#)
- [Video - Grease Best PRactices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-625ETPN38T-SPEC-EN | REV 6/2024