



25/28 kV 600 Amp 3-pt Junction Bracket.

By Hubbell
Catalog # [625J3B](#)



25/28 kV 600 Amp 3-pt Junction Bracket.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	Brackets
Number of Positions	3
Type	600 Amp Dead Break
UPC	096359393252

Dimensions

Weight	12.75 lb
--------	----------

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	600 A
kV Class	25/28 kV;15 kV

Logistics

Pallet Quantity	25
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - 600A Deadbreak Junction](#)
- [Sales Drawings - JUNCTIONS, 25/28KV 600A](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)
- [Video - Grease Best Practices](#)



A Hubbell brand