



25/28 kV 600 Amp 4-pt Junction Bracket.

By Hubbell
Catalog # [625J4B](#)



25/28 kV 600 Amp 4-pt Junction Bracket.

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

EU RoHS Indicator	No
Mounting Type	Brackets
Number of Positions	4
Type	600 Amp Dead Break
UPC	096359393283

Dimensions

Dimensions	19.50 in x 7.00 in x 7.00 in
Height	7 in
Length	19.5 in
Weight	16.5 lb
Width	7 in

Electrical Ratings

AC Withstand Voltage (1 min)	40 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	19 kV
Current Rating	600 A
kV Class	25/28 kV;15 kV

Logistics

Pallet Quantity	25
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Installation Manuals - 600A Deadbreak Junction](#)
- [Sales Drawings - JUNCTIONS, 25/28KV 600A](#)
- [SDS - VERSILUBE G661 SILICONE COMPOUND](#)
- [Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A](#)
- [Video - Grease Best PRactices](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
HubbellBrand-625J4B-SPEC-EN | REV 6/2024