



Modular Splice Kit, Three Way

By Hubbell
Catalog # [625L3](#)

600 Amp Three-way Modular Splice Kit.



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359393320
With Test Point	No

Dimensions

Weight	23.75 lb
--------	----------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	25/28 kV

Logistics

Pallet Quantity	25
Standard Package	1

Product Assets

[Catalogs - Cable Accessories](#)
[Sales Drawings - Module Splicing Kits 600/900 AMP, 25 KV](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Video - Grease Best PRactices](#)



A Hubbell brand