

25/28 kV LRTP Kit w/ Test Point
and Jacket Seal Kit

By Hubbell Power Systems
Catalog # [625LRTPLM28TJ](#)

25/28 kV 600 Amp Load Break Reducing Tap Plug Kit with Test Point. Cable insulation range 1.280 in - 1.430 in. Kit includes T-body, insulating plug with cap, compression lug, threaded stud, and cable adapter

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

Catalog Number	625LRTPLM28TJ
Connector Type	Aluminum Threaded
Type	600 Amp Dead Break
With Seal Kit	Yes
With Test Point	Yes

Dimensions

Weight	10 lb
--------	-------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
------------------------------	-------

Specifications

Basic Impulse Level	125 kV
---------------------	--------

Corona Extinction (3pC)	21 kV
-------------------------	-------

Current Rating	600 A
----------------	-------

kV Class	25/28 kV
----------	----------

Conductor Related

Solid or Compacted Conductor	300
------------------------------	-----

Stranded or Compressed Conductor	250
----------------------------------	-----

Logistics

Standard Package	1
------------------	---

Product Assets

Catalogs - Cable Accessories	
------------------------------	--

Specifications - 625LRTPLM28TJ	
--------------------------------	--

Test Documents - Cable Accessories Test Report - 15kV & 25kV 600A	
---	--

Video - Hubbell Power Systems In Depth: Proper Torque for Underground Cable Accessories	
---	--

Video - Hubbell Power Systems T-Body Connector Assembly	
---	--

Video - Hubbell Power Systems In Depth: T-Body Kits	
---	--



*Representative Image