



BI-Metal

By Hubbell
Catalog # [625LUGB41](#)

BI-Metal Lug, 600A, Conductor Range = 1000 Stranded or Compressed and 1100 Compact



Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

| | |
|----------------|------------------|
| Connector Type | Bi-Metal |
| Type | 600Amp DeadBreak |
| UPC | 096359438366 |

Dimensions

| | |
|--------|---------|
| Weight | 0.45 lb |
|--------|---------|

Electrical Ratings

| | |
|----------------|-------|
| Current Rating | 600 A |
|----------------|-------|

Conductor Related

| | |
|----------------------------------|------|
| Solid or Compacted Conductor | 1100 |
| Stranded or Compressed Conductor | 1000 |

Logistics

| | |
|------------------|---|
| Standard Package | 3 |
|------------------|---|

Product Assets

[Video - Grease Best PRactices](#)