



25/28 kV 600 Amp T-Body without Stud.

By Hubbell
Catalog # [625TBN](#)

25/28 kV 600 Amp T-Body without Stud.



*Representative Image

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. 592 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible
- Optional features include test point, shear bolt connector, cold shrink jacket seal kit or shield adapter kit

General

EU RoHS Indicator	No
Type	600 Amp Dead Break
UPC	096359438380
With Test Point	No

Dimensions

Weight	4.75 lb
--------	---------

Electrical Ratings

AC Withstand Voltage (1 min)	45 kV
Basic Impulse Level	125 kV
Corona Extinction (3pC)	21 kV
Current Rating	600 A
kV Class	15 kV

Logistics

Carton Quantity	9
Standard Package	1

Product Assets

[Catalogs - Cable Accessories](#)
[Sales Drawings - Elbow Housing 600A,25KV](#)
[SDS - VERSILUBE G661 SILICONE COMPOUND](#)
[Video - Grease Best PRactices](#)



A Hubbell brand