

Sure-Direct™ 35 kV Class 600 A
Deadbreak Elbow Arrester (22 kV
MCOV)

By Hubbell Power Systems
Catalog # [635EDA220](#)



DEADBREAK ELBOW ARRESTER, 35KV, 600 A, 22 MCOV,
Mates with IEEE Std. 386, Interface 13. Sure-Direct™

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	635EDA220
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Type	Underground Arresters
UPC	096359764281

Dimensions

Height	13.7 in
Maximum Operating Altitude	6000 ft
Weight	6.5 lb

Electrical Ratings

Duty Cycle	27 kV
MCOV	22 kV
Maximum Discharge Voltage	• 70.8 kV @ 1.5 kA

- 75.4 kV @ 3 kA
- 80.4 kV @ 5 kA
- 90.5 kV @ 10 kA
- 104.6 kV @ 20 kA
- 130.7 kV @ 40 kA

Maximum Switching Surge Protective Level @ 500A	69 kV
kV Class	35 kV

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	54
Standard Package	1

Product Assets

[Installation Manuals - Hubbell Deadbreak Elbow Arrester 600 A / 900 A, 35 kV Class Interface](#)
[Sales Drawings - 35 kV Deadbreak Elbow Arrester](#)
[Specifications - 635EDA220](#)
[Video - Hubbell Power Systems Elbow Arrester](#)
[Video](#)