

Sure-Direct™ 35 kV Class 600 A
Deadbreak Elbow Arrester (27 kV
MCOV)

By Hubbell Power Systems
Catalog # [635EDA270](#)



DEADBREAK ELBOW ARRESTER, 35KV, 600 A, 27 MCOV,
Mates with IEEE Std. 386, Interface 13. Sure-Direct™

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	635EDA270
Grounding Style	36 in Line Lead
Type	Underground Arresters
UPC	096359809357

Dimensions

Height	13.7 in
--------	---------

Electrical Ratings

Duty Cycle	33 kV
MCOV	27 kV
Maximum Discharge Voltage	• 107.6 kV @ 1.5 kA

- 92.2 kV @ 3 kA
- 98.3 kV @ 5 kA
- 110.7 kV @ 10 kA
- 127.9 kV @ 20 kA
- 159.8 kV @ 40 kA

Maximum Switching Surge Protective Level @ 500A	77.5 kV
kV Class	35 kV

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Logistics

Pallet Quantity	64
Standard Package	1

Product Assets

[Sales Drawings - 35 kV Deadbreak Elbow Arrester](#)
[Specifications - 635EDA270](#)
[Video - Hubbell Power Systems Elbow Arrester](#)
[Video](#)