



Sure-Direct™ 35 kV Class 600 A Deadbreak Elbow Arrester (29 kV MCOV)

By Hubbell
Catalog # [635EDA290](#)



DEADBREAK ELBOW ARRESTER, 35KV, 600 A, 29 MCOV,
Mates with IEEE Std. 386, Interface 13. Sure-Direct™

Features

- Meets or Exceeds IEEE Std. 386 and IEEE Std. C62.11. Section 8.1 requirements
- Interchangeable with other products meeting the same requirements
- Fully shielded, insulated and submersible

General

Catalog Number	635EDA290
EU RoHS Indicator	No
Grounding Style	36 in Line Lead
Type	Underground Arresters
UPC	096359764274

Dimensions

Height	13.7 in
--------	---------

Electrical Ratings

Duty Cycle	36 kV
MCOV	29 kV
Maximum Discharge Voltage	<ul style="list-style-type: none">• 117.4 kV @ 1.5 kA• 100.5 kV @ 3 kA• 107.2 kV @ 5 kA• 120.7 kV @ 10 kA• 139.4 kV @ 20 kA• 174.3 kV @ 40 kA
Maximum Switching Surge Protective Level @ 500A	84.5 kV
kV Class	35 kV

Logistics

Pallet Quantity	54
Standard Package	1

Product Assets

- [Catalogs - Cable Accessories](#)
- [Sales Drawings - 35 kV Deadbreak Elbow Arrester](#)
- [Specifications - 635EDA290](#)