

38kV Liberty™ Three Phase Ganged
Recloser

By Hubbell Power Systems

38kV, 170kV BIL, 800A, 16kA Three-Phased Ganged RecloserThe Liberty™ 3GR consist of three gang operated vacuum switches in a single housing design. The housing is constructed of welded and riveted stainless-steel painted ANSI 70 with a zinc primer for maximum strength and corrosion resistance

Features

- Solid Dielectric Vacuum Interrupter Technology
- Integrated Sensing (6 Voltage Sensors and 3 Current Sensors)
- Single 32-pin Connector
- Semaphore and Mechanical Counter
- Manual Operation and Lockout Handle
- Our One Hubbell site-ready solution offers an integrated solution consisting of controllers, cables, and switching devices assembled, configured, integrated, and tested ready to meet your needs
-

Application

The LIBERTY™ 3Ø Ganged Recloser is site-ready solution that can be customized to fit your application. The 3GR is designed for three-phase fault interuppting applications.

General

Ambient Temp. Range	-40°C to +60 °C
Available Options	Control Power Transformers, Surge Arrestors, Wildlife



Mounting Type

guards, Power and Control cables

- Center mount
- Side mount
- Substation mount

Type

Overhead Solid Dielectric Switches

Electrical Ratings

Amperage Rating	800 A
BIL	170 kV
Current Rating	800 A
Frequency Rating	50/60 Hz
Voltage Rating	Max 38 kV

Product Assets

- [Catalogs - Liberty™ HB Series Overhead Solid Dialelectric Switches](#)
- [Literature - Liberty™ HB Series Three Phase Recloser](#)
- [Specifications - 38kV Liberty™ Three Phase Ganged Recloser](#)