

Dome Closure 350 All Dielectric

By Hubbell Power Systems
Catalog # [PSCA350S](#)

Dome Closure 350 All Dielectric



Features

- Splice capacity: 96 single fusion / 288 mass fusion
- Backbone cable ports accept up to .625" OD
- Lateral cable ports accept up to .625" OD
- Factory equipped for butt splice application
- Additional cables can be added with cable build out kit

General

Catalog Number	PSCA350S
Diameter - Cable for Backbone	0.625"
Ports - Maximum	
Diameter - Cable for Lateral	0.625"
Ports - Maximum	
Number Of Ports	4
Number of Trays - Maximum	4
Single Fusion Splice Capacity - Maximum	96
UPC	096359707707

Dimensions

Dimensions	21.608 in x 8.575 in x 5.963 in
Height	5.963 in
Length	21.608 in
Weight	7 lb
Width	8.575 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	48
Standard Package	1

Product Assets

- [Catalogs - Fiber Splice Closures](#)
- [Literature - SF09155E 350 Splice Closure](#)
- [Sales Drawings - PSCA350S CC-27210](#)
- [Specifications - PSCA350S](#)
- [Video - Hubbell Power Systems 350 & 570G Fiber Optic Splice Closures](#)