

Dome Closure 570 All Dielectric

By Hubbell Power Systems
Catalog # [PSCA570S](#)



Dome Closure 570 All Dielectric

*Representative Image

Features

- Splice capacity: 432 single fusion / 1152 mass fusion
- Backbone cable ports accept up to .875" OD
- Lateral cable ports accept up to .750" OD
- Factory equipped to support 2 backbone and 2 lateral cables
- Additional cables can be added with cable build out kit

General

Catalog Number	PSCA570S
Diameter - Cable for Backbone Ports - Maximum	0.875"
Diameter - Cable for Lateral Ports - Maximum	0.750"
Number Of Ports	6
Number of Trays - Maximum	8
Series	570
Single Fusion Splice Capacity - Maximum	432
UPC	096359648505

Dimensions

Dimensions	24.550 in x 10.726 in x 7.160 in
Height	7.16 in
Length	24.55 in
Weight	13 lb
Width	10.726 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	16
Standard Package	1

Product Assets

- [Catalogs - Fiber Splice Closures](#)
- [Sales Drawings - PSCA570S CC-27108](#)
- [Specifications - PSCA570S](#)
- [Video - Hubbell Power Systems 570 & 790 Splice Closures](#)