

Dome Closure 570 All Dielectric,
Grommets

By Hubbell Power Systems
Catalog # [PSCA570SG](#)



Dome Closure 570 All Dielectric, Grommets

Features

- Splice capacity: 432 single fusion / 1152 mass fusion
- Backbone cable ports accept up to .750" OD
- Lateral cable ports accept up to .625" OD
- 2 Grommet bags and stand offs for butt splice included
- Additional cables can be added with cable build out kit

General

Catalog Number	PSCA570SG
Diameter - Cable for Backbone	0.750"
Ports - Maximum	
Diameter - Cable for Lateral	0.625"
Ports - Maximum	
Number Of Ports	6
Number of Trays - Maximum	8
Single Fusion Splice Capacity - Maximum	432
UPC	096359748625

Dimensions

Dimensions	24.550 in x 10.726 in x 7.160 in
------------	----------------------------------

Height	7.16 in
Length	24.55 in
Weight	16.8 lb
Width	10.726 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	20
Standard Package	1

Product Assets

[Catalogs - Fiber Splice Closures](#)
[Installation Manuals - TD09169E ADSS and Isolated G Series Inst Literature - HUBBELL® 570 GROMMET SPLICE CLOSURE](#)
[Sales Drawings - PSCA570SG CC-27212](#)
[Specifications - PSCA570SG](#)
[Video - Hubbell Power Systems 350 & 570G Fiber Optic Splice Closures](#)