

Dome Closure 790 All Dielectric

By Hubbell Power Systems  
Catalog # [PSCA790SEB](#)



Dome Closure 790 All Dielectric

\*Representative Image

Features

- Splice capacity: 648 single fusion / 1728 mass fusion
- Backbone cable ports accept up to 1.250" OD
- Lateral cable ports accept up to .875" OD
- Factory equipped to support 2 backbone and 2 lateral cables
- Additional cables can be added with cable build out kit

General

Catalog Number	PSCA790SEB
Diameter - Cable for Backbone Ports - Maximum	1.250"
Diameter - Cable for Lateral Ports - Maximum	0.875"
Number Of Ports	8
Number of Trays - Maximum	12
Series	790
Single Fusion Splice Capacity - Maximum	648
UPC	096359647287

Dimensions

Dimensions	26.542 in x 12.716 in x 9.300 in
Height	9.3 in
Length	26.542 in
Weight	19 lb
Width	12.716 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	16
Standard Package	1

Product Assets

- [Catalogs - Fiber Splice Closures](#)
- [Sales Drawings - PSCA790SEB CC-27411](#)
- [Specifications - PSCA790SEB](#)
- [Video - Hubbell Power Systems 570 & 790 Splice Closures](#)