

Dome Closure 790 Grounded

By Hubbell Power Systems
Catalog # [PSCG790SEB](#)

Dome Closure 790 Grounded



Features

- Splice capacity: 648 single fusion / 1728 mass fusion
- Backbone cable ports accept up to 1.250" OD
- Lateral cable ports accept up to .875" OD
- Factory equipped to support 2 backbone and 2 lateral cables
- Utilizes a threaded stud bonding point

General

Catalog Number	PSCG790SEB
Diameter - Cable for Backbone	1.250"
Ports - Maximum	
Diameter - Cable for Lateral	0.875"
Ports - Maximum	
Number Of Ports	8
Number of Trays - Maximum	12
Single Fusion Splice Capacity - Maximum	648
UPC	096359837794

Dimensions

Dimensions	24 in x 10 in x 7.5 in
Height	7.5 in
Length	24 in
Width	10 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Carton Quantity	1
Standard Package	1

Product Assets

[Catalogs - Fiber Splice Closures](#)
[Literature - Hubbell® PSCG Splice Closures](#)
[Specifications - PSCG790SEB](#)