

Dome Closure 570 OPGW Standard
Tray Holder

By Hubbell Power Systems
Catalog # [PSCO5702xxxxyyS](#)



DOMECLOSURE 570 OPGW STANDARD TRAY HOLDER
(Replace xxx with OD of OPGW and yyy with OD of central tube
(if SS tubes, “000”))

Features

- Splice capacity: 192 single fusion / 576 mass fusion
- OPGW ports accept up to .687" OD
- ADSS or buried backbone cable ports accept up to .875" OD
- ADSS or buried lateral cable ports accept up to .750" OD

General

Catalog Number	PSCO5702xxxxyyS
Diameter - Cable for Backbone	0.687"
Ports - Maximum	
Diameter - Cable for Lateral	0.750"
Ports - Maximum	

Number Of Ports	6
Number of Cables - Maximum	4
Number of Trays - Maximum	8
Single Fusion Splice Capacity - Maximum	192

Product Assets

[Catalogs - Fiber Splice Closures](#)
[Specifications - PSCO5702XXXXYYYS](#)
[Video - Hubbell Power Systems 570 Splice Closures for OPGW Cable](#)