



HCO0710377

By Hubbell Industrial Controls
Catalog # [HCO0710377](#)



TYPE 2210 SPEED RESPONSIVE SWITCH, C SERIES, CENTRIFUGAL ACTION, FLYWEIGHT OPERATED, NON-DIRECTIONAL AC OR DC CONTACTS, NEMA 7 EXPLOSION-PROOF CLASS 1, GROUPS C OR D, 2 MANUAL RESETS, DOUBLE SPEED RATIO INCREASED (8.64 TO 1)

General

Enclosure Type	Fiberglass Reinforced Polyester Resin And/Or Cast Aluminum
Series	2210, C
Type	Non-Directional, AC/DC

Electrical Ratings

Current / Amperage Rating	10 A
Current Rating	10 A

Certifications and Compliance

Enclosure NEMA Rating	7 EXPLOSION-PROOF, CLASS 1, GRP C, D
-----------------------	--------------------------------------

Product Assets

[Catalogs - 2210 Speed Switches Specifications](#)
[Catalogs - 2200/2300 Speed Switches Catalog](#)
[Catalogs - 2210 Speed Switches Price List](#)
[Installation Manuals - ICD_Pub131_CATALOG](#)
[Installation Manuals - ICD_Pub130_CATALOG](#)
[Installation Manuals - ICD_Pub134_CATALOG](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
ICD-HCO0710377-SPEC-EN | REV 5/2023